



● Material/Finish



	NSBU
Main Body	Urethane (Black) Shore Hardness A90
Hex Socket Head Cap Screw with Low Profile	S45C Trivalent Chromate Treatment
Collar	SUS304

- Replacement parts for stoppers for linear guides with urethane. For replacement when the urethane part has deteriorated.
- Usable with the Stoppers for Linear Guides with Urethane series.
- Hex socket head cap screws with low profile and collars for mounting are provided with all products.

Unit : mm

Part Number	D	D1	D2	H	U	Hex Socket Head Cap Screw with Low Profile	Mass (g)
<b>NSBU-15</b>	15	7.6	6.2	11	8	M4×10	5.4
<b>NSBU-20</b>	20	9.2	7.2	13	9	M5×12	9.6
<b>NSBU-25</b>	25	9.2	7.2	13	9	M5×12	12.6

● Part Number Specification

**NSBU-20**



Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant	Laser Marking
Not Available	Not Available	Not Available	Not Available	Not Available