



- High quality / high-precision. Soft impression of matte black.
- Convenient long size.
- Types and thread part materials can be selected by a product code.

Product Code <b>1</b>	Type	Thread Part Material
<b>KLM</b>	Male Screw	Made of Steel
<b>KLMS</b>	Male Screw	Made of Stainless Steel
<b>KLF</b>	Female Screw	Made of Steel
<b>KLFS</b>	Female Screw	Made of Stainless Steel



• Material/Finish



	<b>KLM</b>	<b>KLMS</b>	<b>KLF</b>	<b>KLFS</b>
Knob	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)
Thread Part	SWCH10R Trivalent Chromate Treatment	SUSXM7	Steel Trivalent Chromate Treatment	SUS303

Dimensions

**KLM** **KLMS** Male Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D <b>2</b>	M (Coarse)		H	s	d	Mass (g)
			Nominal of Thread <b>3</b>	Pitch				
<b>KLM-20-M5</b>	<b>KLMS-20-M5</b>	20	M5	0.8	25	12	13	8 - 9
<b>KLM-20-M6</b>	<b>KLMS-20-M6</b>	20	M6	1	25	12	13	9 - 13
<b>KLM-25-M5</b>	<b>KLMS-25-M5</b>	25	M5	0.8	28	15	16	12 - 13
<b>KLM-25-M6</b>	<b>KLMS-25-M6</b>	25	M6	1	28	15	16	13 - 16
<b>KLM-25-M8</b>		25	M8	1.25	28	15	16	20 - 22
<b>KLM-32-M6</b>	<b>KLMS-32-M6</b>	32	M6	1	32	17	20	19 - 20
<b>KLM-32-M8</b>	<b>KLMS-32-M8</b>	32	M8	1.25	32	17	20	23 - 33
<b>KLM-32-M10</b>		32	M10	1.5	32	17	20	40 - 46

**KLF** **KLFS** Female Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D <b>2</b>	M (Coarse)		Lf	H	s	d	Mass (g)
			Nominal of Thread <b>3</b>	Pitch					
<b>KLF-20-M5</b>		20	M5	0.8	10	25	12	13	10
<b>KLF-20-M6</b>	<b>KLFS-20-M6</b>	20	M6	1	14	25	12	13	9
<b>KLF-25-M5</b>		25	M5	0.8	15	28	15	16	20
<b>KLF-25-M6</b>		25	M6	1	15	28	15	16	19
<b>KLF-25-M8</b>	<b>KLFS-25-M8</b>	25	M8	1.25	18	28	15	16	15
<b>KLF-32-M6</b>		32	M6	1	18	32	17	20	41
<b>KLF-32-M8</b>		32	M8	1.25	18	32	17	20	38
<b>KLF-32-M10</b>	<b>KLFS-32-M10</b>	32	M10	1.5	20	32	17	20	33

**KLM** Made of Steel **KLMS** Made of Stainless Steel

Part Number Male Screw	Lm (mm) <b>4</b>						
	10	16	20	25	30	40	
<b>KLM-20-M5</b>	●	●	●				
<b>KLM-20-M6</b>	●	●	●		●		
<b>KLM-25-M5</b>			●	●			
<b>KLM-25-M6</b>		●	●	●	●		
<b>KLM-25-M8</b>			●	●			
<b>KLM-32-M6</b>			●	●			
<b>KLM-32-M8</b>		●	●	●	●	●	
<b>KLM-32-M10</b>					●	●	
<b>KLMS-20-M5</b>		●	●				
<b>KLMS-20-M6</b>	●	●	●				
<b>KLMS-25-M5</b>			●	●			
<b>KLMS-25-M6</b>		●	●	●			
<b>KLMS-32-M6</b>			●	●			
<b>KLMS-32-M8</b>		●	●	●			

• Part number specification

**KLM-32-M6-25**  
**1** **2** **3** **4**

For male screw type, select **4** screw length Lm from the sizes marked with ● in the table.

Cleanroom Wash & Packaging → P.0000 Screw Combination → P.0000 Screw Length Adjustment → P.0000 Vibration Resistant → P.0000 Laser Marking → P.0000  
 Please feel free to contact us Female screw only/ Add'l charge Male screw only/ Add'l charge Male screw only/ Add'l charge Available / Add'l charge