



- A wide variety of screw sizes from M3 to M10.
- Equivalent to SUS316L. For applications including food machinery, packaging machinery, etc., where corrosion resistance is called for.

• To distinguish **KNMS** (SUS303) from **KNML** (SUS316L equivalent), **KNML** has a groove on its seating surface.

• Material/Finish



	<b>KNML</b>
Main Body	Equivalent to SUS316L

## Dimensions

Unit : mm

Part Number <span style="color:red">1</span>	D	M (Coarse)		H	s	A	d	Mass (g)
		Nominal of Thread	Pitch					
<b>KNML-12-M3</b>	12	M3	0.5	7.5	5	2.5	6	3 - 4
<b>KNML-16-M4</b>	16	M4	0.7	9.5	6	3.5	8	9 - 10
<b>KNML-20-M5</b>	20	M5	0.8	11.5	7.5	4	10	15 - 16
<b>KNML-24-M6</b>	24	M6	1	15	10	5	12	28 - 32
<b>KNML-30-M8</b>	30	M8	1.25	18	12	6	16	58 - 61
<b>KNML-36-M10</b>	36	M10	1.5	23	15	8	20	108 - 120

Part Number	Lm (mm) <span style="color:red">2</span>						
	6	10	16	20	25	30	40
<b>KNML-12-M3</b>	●	●	●				
<b>KNML-16-M4</b>	●	●	●				
<b>KNML-20-M5</b>		●	●	●			
<b>KNML-24-M6</b>		●	●	●	●	●	
<b>KNML-30-M8</b>			●	●	●	●	
<b>KNML-36-M10</b>				●	●	●	●

• Part Number Specification

**KNML-24-M6 - 20**



For 2 screw length Lm, select from the sizes marked with ● in the table.

Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant	Laser Marking
Please feel free to contact us	Not Available	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge