



- Set collar for securing bearing.
- It can be fixed by pressing the bearing inner wheel only on the convex of the main body.
- Optimal for securing bearing when it is difficult to fix the snap ring, etc. to the shaft.
- It is attached to the shaft by the set screws.

● Material/Finish



	NSC-CB	NSC-MB
Main body	S45C Ferroferric Oxide Film (Black)	S45C Electroless Nickel Plating
Hex Socket Set Screw	SCM435 Ferroferric Oxide Film (Black)	SUSXM7



Part Number	Part Number	d	B	B1	D	D1	M (coarse) *1	Applicable bearings	Mass (g)
Ferroferric oxide film	Electroless nickel plating	Unit : mm							
NSC-3-7-CB	NSC-3-7-MB	3	7.5	5	7	5	M3	693ZZ · 623ZZ	1
NSC-4-7-CB	NSC-4-7-MB	4	7.5	5	8	6	M3	694ZZ · 624ZZ	2
NSC-5-7-CB	NSC-5-7-MB	5	7.5	5	11	7.2	M3	695ZZ · 605ZZ · 625ZZ	4
NSC-6-7-CB1	NSC-6-7-MB1	6	7.5	5	13	8.4	M3	606ZZ	4
NSC-6-7-CB2	NSC-6-7-MB2	6	7.5	5	13	9.2	M3	626ZZ	5
NSC-6-7-CB3	NSC-6-7-MB3	6	7.5	5	13	8	M3	696ZZ	6
NSC-8-9-CB1	NSC-8-9-MB1	8	9.5	7	18	11.7	M4	608ZZ	12
NSC-8-9-CB2	NSC-8-9-MB2	8	9.5	7	18	11.4	M4	628ZZ	11
NSC-8-9-CB3	NSC-8-9-MB3	8	9.5	7	18	10.4	M4	698ZZ	11
NSC-10-11-CB1	NSC-10-11-MB1	10	11	8	20	14.2	M5	6000ZZ	16
NSC-10-11-CB2	NSC-10-11-MB2	10	11	8	20	16.7	M5	6200ZZ	18
NSC-10-11-CB3	NSC-10-11-MB3	10	11	8	20	13.2	M5	6900ZZ	15
NSC-12-11-CB1	NSC-12-11-MB1	12	11	8	22	17.2	M5	6001ZZ	19
NSC-12-11-CB2	NSC-12-11-MB2	12	11	8	22	17.7	M5	6201ZZ	19
NSC-12-11-CB3	NSC-12-11-MB3	12	11	8	22	15.2	M5	6901ZZ	17
NSC-15-11-CB1	NSC-15-11-MB1	15	11	8	25	20.2	M5	6002ZZ	22
NSC-15-11-CB2	NSC-15-11-MB2	15	11	8	25	21.2	M5	6202ZZ	23
NSC-15-11-CB3	NSC-15-11-MB3	15	11	8	25	18.7	M5	6902ZZ	21

*1 : Hex socket set screw is provided.
*1 : If d dimension is 5 or below, one point.

Part Number	Part Number	d	B	B1	D	D1	M (coarse) *1	Applicable bearings	Mass (g)
Ferroferric oxide film	Electroless nickel plating	Unit : mm							
NSC-17-13-CB1	NSC-17-13-MB1	17	13	10	28	22.2	M6	6003ZZ	33
NSC-17-13-CB2	NSC-17-13-MB2	17	13	10	28	24.2	M6	6203ZZ	35
NSC-17-13-CB3	NSC-17-13-MB3	17	13	10	28	20.2	M6	6903ZZ	31
NSC-20-13-CB1	NSC-20-13-MB1	20	13	10	35	25.2	M6	6004ZZ	52
NSC-20-13-CB2	NSC-20-13-MB2	20	13	10	35	27.2	M6	6204ZZ	54
NSC-20-13-CB3	NSC-20-13-MB3	20	13	10	35	24.7	M6	6904ZZ	52
NSC-25-13-CB1	NSC-25-13-MB1	25	13.5	10	38	31.2	M6	6005ZZ	55
NSC-25-13-CB2	NSC-25-13-MB2	25	13.5	10	38	33.2	M6	6205ZZ	58
NSC-25-13-CB3	NSC-25-13-MB3	25	13.5	10	38	30.2	M6	6905ZZ	54
NSC-30-15-CB1	NSC-30-15-MB1	30	15.5	12	45	38.2	M8	6006ZZ	90
NSC-30-15-CB2	NSC-30-15-MB2	30	15.5	12	45	40.2	M8	6206ZZ	94
NSC-30-15-CB3	NSC-30-15-MB3	30	15.5	12	45	35.2	M8	6906ZZ	86
NSC-35-16-CB1	NSC-35-16-MB1	35	16.5	12	50	43.2	M8	6007ZZ	106
NSC-35-16-CB2	NSC-35-16-MB2	35	16.5	12	50	46.2	M8	6207ZZ	114
NSC-35-16-CB3	NSC-35-16-MB3	35	16.5	12	50	41.2	M8	6907ZZ	101
NSC-40-18-CB1	NSC-40-18-MB1	40	18.5	14	60	48.2	M10	6008ZZ	183
NSC-40-18-CB2	NSC-40-18-MB2	40	18.5	14	60	52.2	M10	6208ZZ	195
NSC-40-18-CB3	NSC-40-18-MB3	40	18.5	14	60	46.2	M10	6908ZZ	179

*1 : Hex socket set screw is provided.
*1 : If d dimension is 5 or below, one point.

Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge

● Part number specification

NSC-4-7-CB

