


SNSS-MO Hex Socket Head Cap Screws - MoS₂ Coating




Seizing Prevention SUS Stainless steel



- Tightening property (reference)
Part Number : SNSS-M5 - 25-MO

➔ P.xxxx



- Excellent corrosion resistance and abrasion resistance.
- The coating has excellent lubricating ability and is intended to prevent seizing of screws.
- Conforms to JIS B 1176, ISO 4762, and DIN 912.

● Application

Seizing prevention
FPD production equipment, semiconductor devices,
and general industrial machines

● Material/Finish



	SNSS-MO
Main Body	SUSXM7 (Equivalent to SUS304) Molybdenum Disulfide Coating
Strength Class	A2-70

Unit : mm

Part Number	M (Coarse)		L												D1	L1	B	Mass (g)	Qty per pack			
	Nominal of Thread	Pitch	5	6	8	10	12	16	20													
SNSS-M3-MO	M3	0.5	5	6	8	10	12	16	20									5.5	3	2.5	0.67 - 1.4	10
SNSS-M4-MO	M4	0.7		6	8	10	12	16	20	25								7	4	3	1.5 - 3.2	10
SNSS-M5-MO	M5	0.8			8	10	12	16	20	25								8.5	5	4	2.5 - 4.8	10
SNSS-M6-MO	M6	1				10	12	16	20	25	30							10	6	5	4.7 - 8.3	10
SNSS-M8-MO	M8	1.25						16	20	25	30	35						13	8	6	12 - 19	10
SNSS-M10-MO	M10	1.5							20	25	30	35	40					16	10	8	23 - 33	10

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

SNSS-M5-16-MO

Product Code	➔	➔	Product Code
--------------	---	---	--------------

Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Please feel free to contact us