



- Set screw type set collars.
 - Fastening to the shaft is done with set screws.
 - Chamfering on one end is larger (bore diameter 8mm or above).
- When fixing the bearing, this avoids interference between the set collar and the outer ring.



● Material/Finish



	NSC-C	NSC-M	NSC-S
Main Body	S45C Ferroferric Oxide Film (Black)	S45C Electroless Nickel Plating	SUS304
Hex Socket Set Screw	SCM435 Ferroferric Oxide Film (Black)	SUSXM7	SUSXM7

NSC-C Made of Steel, Ferroferric Oxide Film **NSC-M** Made of Steel, Electroless Nickel Plating **NSC-S** Made of Stainless Steel Unit : mm

Part Number	Part Number	Part Number	d	B	D	D ₁	M (Coarse)*1	Number of Set Screws	Mass (g)
NSC-3-5-C	NSC-3-5-M	NSC-3-5-S	3	5	7	-	M3	1	1
NSC-3-6-C	NSC-3-6-M	NSC-3-6-S	3	6	7	-	M3	1	1
NSC-3-8-C	NSC-3-8-M	NSC-3-8-S	3	8	7	-	M3	1	2
NSC-4-5-C	NSC-4-5-M	NSC-4-5-S	4	5	8	-	M3	1	1
NSC-4-6-C	NSC-4-6-M	NSC-4-6-S	4	6	12	-	M4	1	5
NSC-4-8-C	NSC-4-8-M	NSC-4-8-S	4	8	12	-	M4	1	6
NSC-5-5-C	NSC-5-5-M	NSC-5-5-S	5	5	11	-	M3	1	3
NSC-5-6-C	NSC-5-6-M	NSC-5-6-S	5	6	14	-	M4	1	6
NSC-5-8-C	NSC-5-8-M	NSC-5-8-S	5	8	14	-	M4	1	8
NSC-5-10-C	NSC-5-10-M	NSC-5-10-S	5	10	14	-	M4	1	10
NSC-6-5-C	NSC-6-5-M	NSC-6-5-S	6	5	12	-	M3	2	3
NSC-6-6-C	NSC-6-6-M	NSC-6-6-S	6	6	15	-	M4	1	6
NSC-6-8-C	NSC-6-8-M	NSC-6-8-S	6	8	15	-	M4	1	9
NSC-6-10-C	NSC-6-10-M	NSC-6-10-S	6	10	16	-	M4	1	13
NSC-8-5-C	NSC-8-5-M	NSC-8-5-S	8	5	14	-	M3	2	4
NSC-8-6-C	NSC-8-6-M	NSC-8-6-S	8	6	16	13	M4	2	6
NSC-8-8-C	NSC-8-8-M	NSC-8-8-S	8	8	16	13	M4	2	9
NSC-8-10-C	NSC-8-10-M	NSC-8-10-S	8	10	18	13	M4	2	16
NSC-10-5-C	NSC-10-5-M	NSC-10-5-S	10	5	16	-	M3	2	5
NSC-10-6-C	NSC-10-6-M	NSC-10-6-S	10	6	18	16	M4	2	8
NSC-10-8-C	NSC-10-8-M	NSC-10-8-S	10	8	18	16	M4	2	10
NSC-10-10-C	NSC-10-10-M	NSC-10-10-S	10	10	20	16	M4	2	17
NSC-12-6-C	NSC-12-6-M	NSC-12-6-S	12	6	20	-	M4	2	9
NSC-12-8-C	NSC-12-8-M	NSC-12-8-S	12	8	22	20	M4	2	16
NSC-12-10-C	NSC-12-10-M	NSC-12-10-S	12	10	26	20	M5	2	30
NSC-12-12-C	NSC-12-12-M	NSC-12-12-S	12	12	26	20	M6	2	36

*1: Hex socket set screw is provided.

Part Number	Part Number	Part Number	d	B	D	D ₁	M (Coarse)*1	Number of Set Screws	Mass (g)
NSC-13-6-C	NSC-13-6-M	NSC-13-6-S	13	6	20	-	M4	2	8
NSC-13-8-C	NSC-13-8-M	NSC-13-8-S	13	8	22	20	M4	2	15
NSC-13-10-C	NSC-13-10-M	NSC-13-10-S	13	10	26	20	M5	2	28
NSC-14-12-C	NSC-14-12-M	NSC-14-12-S	14	12	26	20	M5	2	33
NSC-15-6-C	NSC-15-6-M	NSC-15-6-S	15	6	24	-	M4	2	12
NSC-15-8-C	NSC-15-8-M	NSC-15-8-S	15	8	25	24	M5	2	19
NSC-15-10-C	NSC-15-10-M	NSC-15-10-S	15	10	25	24	M5	2	24
NSC-15-12-C	NSC-15-12-M	NSC-15-12-S	15	12	28	24	M5	2	39
NSC-16-6-C	NSC-16-6-M	NSC-16-6-S	16	6	24	-	M4	2	11
NSC-16-8-C	NSC-16-8-M	NSC-16-8-S	16	8	28	24	M5	2	24
NSC-16-10-C	NSC-16-10-M	NSC-16-10-S	16	10	28	24	M5	2	31
NSC-16-12-C	NSC-16-12-M	NSC-16-12-S	16	12	28	24	M5	2	37
NSC-17-10-C	NSC-17-10-M	NSC-17-10-S	17	10	30	26	M6	2	35
NSC-17-12-C	NSC-17-12-M	NSC-17-12-S	17	12	32	26	M6	2	49
NSC-18-15-C	NSC-18-15-M	NSC-18-15-S	18	15	32	29	M6	2	61
NSC-20-7-C	NSC-20-7-M	NSC-20-7-S	20	7	30	-	M5	2	21
NSC-20-10-C	NSC-20-10-M	NSC-20-10-S	20	10	32	29	M6	2	36
NSC-20-12-C	NSC-20-12-M	NSC-20-12-S	20	12	32	29	M6	2	83
NSC-20-15-C	NSC-20-15-M	NSC-20-15-S	20	15	32	29	M6	2	55
NSC-22-18-C	NSC-22-18-M	NSC-22-18-S	22	18	38	34	M8	2	101
NSC-25-12-C	NSC-25-12-M	NSC-25-12-S	25	12	38	37	M6	2	60
NSC-25-15-C	NSC-25-15-M	NSC-25-15-S	25	15	38	37	M6	2	73
NSC-25-18-C	NSC-25-18-M	NSC-25-18-S	25	18	42	38	M8	2	122
NSC-28-18-C	NSC-28-18-M	NSC-28-18-S	28	18	45	40	M8	2	129
NSC-30-14-C	NSC-30-14-M	NSC-30-14-S	30	14	45	42	M8	2	91
NSC-30-16-C	NSC-30-16-M	NSC-30-16-S	30	16	45	42	M8	2	106
NSC-30-18-C	NSC-30-18-M	NSC-30-18-S	30	18	49	42	M8	2	156
NSC-30-20-C	NSC-30-20-M	NSC-30-20-S	30	20	49	42	M8	2	175
NSC-32-20-C	NSC-32-20-M	NSC-32-20-S	32	20	53	44	M8	2	206
NSC-35-15-C	NSC-35-15-M	NSC-35-15-S	35	15	50	47	M8	2	111
NSC-35-18-C	NSC-35-18-M	NSC-35-18-S	35	18	55	47	M8	2	187
NSC-35-20-C	NSC-35-20-M	NSC-35-20-S	35	20	59	47	M8	2	256
NSC-38-22-C	NSC-38-22-M	NSC-38-22-S	38	22	64	50	M10	2	330
NSC-40-18-C	NSC-40-18-M	NSC-40-18-S	40	18	60	55	M10	2	213
NSC-40-22-C	NSC-40-22-M	NSC-40-22-S	40	22	72	55	M10	2	438
NSC-45-22-C	NSC-45-22-M	NSC-45-22-S	45	22	75	60	M10	2	445
NSC-50-20-C	NSC-50-20-M	NSC-50-20-S	50	20	70	65	M10	2	284
NSC-50-25-C	NSC-50-25-M	NSC-50-25-S	50	25	79	65	M10	2	537

*1: Hex socket set screw is provided.

● Part Number Specification

NSC-20-10-S



Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Laser Marking
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge