


SEQS Cross Recessed Head Cap Screws with Extra Low Profile - Stainless Steel



Protrusion **SUS** Stainless steel



● Material/Finish



	SEQS
Main Body	SUSXM7 (Equivalent to SUS304)

- Cross recessed head cap screws with extra low profile.
- For space-saving of equipment/devices and applications with limited overhead space.
- QuaStix *1 is used for the cross recess. By using a dedicated bit for QuaStix **SKQB**, the torque transmission is improved, preventing cam-out and damage to the cross recess.*2

*1: QuaStix is a registered trademark of OSG Corporation.

*2: It can be mounted and removed with ordinary Phillips bits.

● Application

Reducing the size of equipment and devices

Unit : mm

Part Number 1	M (Coarse)		L 2			D1	L1	Bit Part No.	Max. Torque *1 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch									
SEQS-M3	M3	0.5	6	8	10	7	0.8	SKQB-1	0.6	0.45 - 0.6	50
SEQS-M4	M4	0.7	8	10	12	8	0.9	SKQB-2	1.2	0.9 - 1.15	50


*1: Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.


● **SKQB** QuaStix Dedicated Bit
(Supports U6.3 Insert Shapes)

Part Number 3	Mass (g)
SKQB-1	7.4
SKQB-2	17

SKQB-1



SKQB-2



● Part Number Specification

SEQS-M3-8 Cross Recessed Head Cap Screws with Extra Low Profile

1 **2**

SKQB-1 Dedicated Bits

3

1 Individual Sales	2 Cleanroom Wash & Packaging	3 Screw Length Adjustment	4 Vibration Resistant	5 Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available