


# SNF-TBZ-SUC Phillips Flat Head Screws for Sheet Metal



● Material/Finish




	<b>SNF-TBZ-SUC</b>
Main Body	SWCH12A Black Trivalent Chromate Treatment




- Phillips flat head screws with cut seating surface.
- Suitable for sheet metal, preventing seating surface and incomplete threads from hitting the bottom when fixing sheet metal.

Normal flat head machine screw



Incomplete thread part hits bottom

SNF-TBZ-SUC



Cut seating surface prevents bottom hitting

- Incomplete thread part has no more than two peaks.
- Bolts for sheet metal are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.

● Application

Reducing the size of equipment and devices


Unit : mm

Part Number <span style="color:red">◀1</span>	M (Coarse)		L <span style="color:red">◀2</span>								D1	L1	Cross-recessed Socket No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
<b>SNF-M3-TBZ-SUC</b>	M3	0.5	4	5	6	8	10				6	1.2	1	0.3 - 0.46	50
<b>SNF-M4-TBZ-SUC</b>	M4	0.7	4	5	6	8	10	12	15		8	1.5	2	0.3 - 1.2	50
<b>SNF-M5-TBZ-SUC</b>	M5	0.8		5	6	8	10	12	15	10	2	2		1.3 - 2.1	20
<b>SNF-M6-TBZ-SUC</b>	M6	1			6	8	10	12	15	12	2.3	2		1.7 - 3.4	20

- When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

**SNF-M5-12-TBZ-SUC**



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available