




SFBS-UC Socket Button Head Cap Screws with Flange for Sheet Metal

Protrusion Easy operation SUS Stainless steel



● Material/Finish



	SFBS-UC
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

● Do not exceed the max. tightening torque.

● Application


Exterior panels on semiconductor manufacturing equipment, etc.
Reducing the size of equipment and devices

● Part Number Specification

SFBS-M5-10-UC



- These stainless steel socket button head cap screws with flange are for fixing thin plates.
- The flange on the head ensures a seating surface even on thin plates with large drilled holes, making fixing possible.
- Because **SFBS-UC** has relief in the under-head area, it is suitable for fixing thin plates. Fastening of thin plates from 0.1mm up is possible.



- For space-saving of equipment/devices and applications with limited overhead space.
- Bolts for fixing thin plates are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.



Unit : mm

Part Number	M (Coarse)		L				D1	D2	L1	t1	B	t	Max. Torque *1 (N·m)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch													
SFBS-M3-UC	M3	0.5	4	5	6	8	7	5.2	1.65	0.5	2	1.05	0.25	0.5 - 0.73	10
SFBS-M4-UC	M4	0.7		5	6	8	9.2	6.8	2.2	0.6	2.5	1.3	0.5	1.1 - 1.4	10
SFBS-M5-UC	M5	0.8			6	8	10	11.4	8.5	2.75	0.8	3	1	2.2 - 2.8	10
SFBS-M6-UC	M6	1			6	8	10	13.6	10.1	3.3	0.9	4	2	3.4 - 4.3	10

*1 : Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available