


SSC-SNS-EL Socket Head Cap Captive Screws - Electroless Nickel Plating



High strength High Specific Strength




● Material/Finish



	SSC-SNS-EL
Main Body	SCM435 Electroless Nickel Plating
Strength Class	12.9

● Installation Example

Make a screw hole in the cover, and then pass the **SSC-SNS-EL** thread part through it. Even when the screw is removed from the frame, **SSC-SNS-EL** does not fall out of the cover because the **SSC-SNS-EL** thread part catches on the cover screw hole.



SSC-SNS-EL Hex socket head cap captive screw

Precautions for Use

- Screw hole inner diameter on the cover side shall be at least the dc dimension.
- The cover thickness should be 0.8mm or above.



- Prevents fall-off and loss of the screw. They are intended to fix protective and inspection covers that are frequently installed and removed.
- For CE Marking compatibility.
- Our unique processing technology enables screws to meet strength class 12.9 after surface treatment.
- For applications that require both high strength (Strength Class 12.9) and corrosion resistance.

● Application


For fixing protective covers and maintenance covers
 CE Marking compatible
 Machine tools / Food machinery / Electrical and electronic equipment

Unit : mm

Part Number	M (Coarse)		L								Lm	D1	L1	B	dc	Mass (g)	
	Nominal of Thread	Pitch															
SSC-SNS-M3-EL	M3	0.5	8	10	12	16					4	5.5	3	2.5	2.2	0.75 - 1.1	
SSC-SNS-M4-EL	M4	0.7		10	12	16	20				5	7	4	3	3	1.7 - 2.4	
SSC-SNS-M5-EL	M5	0.8			12	16	20	25			6	8.5	5	4	3.9	2.8 - 4	
SSC-SNS-M6-EL	M6	1			12	16	20	25	30		8	10	6	5	4.5	4.5 - 5.3	
SSC-SNS-M8-EL	M8	1.25				16	20	25	30	35	40	10	13	8	6	6.3	10 - 14

● Part Number Specification

SSC-SNS-M5-20-EL



Individual Sales 1 piece in 1 pack	Cleanroom Wash & Packaging Available / Add'l charge	Screw Length Adjustment Not Available	Vibration Resistant Not Available	Modification process for captive use with Captive Processing
---------------------------------------	--	--	--------------------------------------	---