


SVFT Phillips Cross Recessed Flat Head Titanium Machine Screws (with Ventilation Hole)



- Vacuum
- Protrusion
- Cleanroom wash & packaging
- Non-Magnetic
- Lightweight



- The ventilation hole easily releases gas trapped in the screw holes of equipment and machines, and supports vacuum drawing of vacuum devices.
- Flat head screw type whose head does not protrude after tightening.
- The surface is reformed by special chemical polishing and bright heat treatment. The amount of outgas is ultralow.
- Nonmagnetic.
- Cleanroom wash and cleanroom packing are completed.
- About bright heat treatment and titanium properties

• Application

Vacuum device / Vacuum container / FPD production device / Semiconductor manufacturing device / Electron microscope

• Material/Finish



SVFT	
Main body	TW270 (Type 1 titanium)


Unit : mm

Part Number 1	M (Coarse)		L 2				D1	L1	d max.	Cross-recessed Socket Number	Mass (g)	Qty per pack
	Nominal of Thread	Pitch	6	8	10	12						
SVFT-M3	M3	0.5	6	8	10		6	1.75	1.2	2	0.18 - 0.23	10
SVFT-M4	M4	0.7	6	8	10	12	8	2.3	1.5	2	0.34 - 0.49	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part number specification

SVFT-M4-12



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Cleanroom washed and packed	Available / Add'l charge	Not Available	Not Available