



● Material/Finish



	SPC-F
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Max. Operating Temperature*1(min./max.): -40/115°C
- PC has low water absorbency and excellent weather resistance.
- The properties and precautions of plastic screws
➔ P.xxxx
- Application

Electrical and electronic equipment and automobiles

Unit : mm

Part Number	M (Coarse)		L 2										D1	L1	Cross-recessed Socket Number	Tension*1 Rupture Load (N)	Torsional*1 Torque (N·m)	Mass (g)	Qty per Pack		
	Nominal of Thread 1	Pitch	4	5	6	8	10	12	15	20	25	30								35	
SPC-M2-F	M2	0.4	4	5	6	8	10								4	1.2	1	107	0.055	0.018 - 0.041	50
SPC-M2.6-F	M2.6	0.45	4	5	6	8	10	12							5.2	1.5	1	196	0.12	0.032 - 0.069	50
SPC-M3-F	M3	0.5	4	5	6	8	10	12	15	20	25				6	1.75	2	266	0.18	0.048 - 0.19	50
SPC-M4-F	M4	0.7			6	8	10	12	15	20	25				8	2.3	2	481	0.39	0.14 - 0.37	50
SPC-M5-F	M5	0.8				8	10	12	15	20	25				10	2.8	2	797	0.8	0.23 - 0.54	50
SPC-M6-F	M6	1					10	12	15	20	25	30	35		12	3.4	3	1136	1.2	0.42 - 1.1	20
SPC-M8-F	M8	1.25						10	12	15	20	25	30		16	4.4	3	2088	3.2	0.87 - 1.9	20

*1: Values in chart are for reference only. They are not guaranteed values. The recommended tightening torque is 50% of the torsional torque.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

SPC-M5-20-F



Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available	Not Available