



● Material/Finish



	<b>SADS-SD</b>
Thread Part	SUS303
Stopper Ring	Equivalent to SUS304

- By combining with female screw products such as a lever and knob, this may be used as a lever or knob of any non-standard screw diameter.
- For screw fixing, use a pin stopper or anaerobic adhesive agent.
- If it is repeatedly tightened in combination with a lever or knob, a pin stopper is recommended.
- Use a stopper ring to accurately determine the threaded length.

## Dimensions

Unit : mm

Part Number	M (Coarse)		M 1 (Coarse)		Lm	s	t	D	Mass (g)
	Nominal of Thread <span style="color:red">①</span>	Pitch	Nominal of Thread <span style="color:red">②</span>	Pitch					
<b>SADS-M4-M5-SD</b>	M4	0.7	M5	0.8	4.5	1.4	0.6	7	1.9 - 6.7
<b>SADS-M5-M4-SD</b>	M5	0.8	M4	0.7	4.5	1.6	0.6	7	1.5 - 3.1
<b>SADS-M5-M6-SD</b>	M5	0.8	M6	1	4.5	1.6	0.6	9	2.7 - 12
<b>SADS-M6-M5-SD</b>	M6	1	M5	0.8	5.5	1.6	0.6	9	2.5 - 7.3
<b>SADS-M6-M8-SD</b>	M6	1	M8	1.25	5.5	2	0.6	9	4.9 - 27
<b>SADS-M8-M6-SD</b>	M8	1.25	M6	1	6.5	2	0.6	9	4.3 - 13
<b>SADS-M8-M10-SD</b>	M8	1.25	M10	1.5	6.5	2.5	0.8	12	10 - 43
<b>SADS-M10-M8-SD</b>	M10	1.5	M8	1.25	8.5	2.5	0.8	12	8.2 - 30
<b>SADS-M10-M12-SD</b>	M10	1.5	M12	1.75	8.5	3	0.8	16	16 - 64

**SADS-SD** Made of Stainless Steel

Part Number	L (mm) <span style="color:red">③</span>									
	12	16	20	25	32	40	50	63	80	
<b>SADS-M4-M5-SD</b>	●	●	●	●	●	●	●			
<b>SADS-M5-M4-SD</b>	●	●	●	●	●					
<b>SADS-M5-M6-SD</b>	●	●	●	●	●	●	●	●		
<b>SADS-M6-M5-SD</b>	●	●	●	●	●	●	●			
<b>SADS-M6-M8-SD</b>	●	●	●	●	●	●	●	●	●	
<b>SADS-M8-M6-SD</b>	●	●	●	●	●	●	●	●		
<b>SADS-M8-M10-SD</b>		●	●	●	●	●	●	●	●	
<b>SADS-M10-M8-SD</b>	●	●	●	●	●	●	●	●	●	
<b>SADS-M10-M12-SD</b>		●	●	●	●	●	●	●	●	

● Part number specification

## SADS-M10-M12-80-SD

Product Code ① ② ③ Thread Size Conversion Type

Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx
Please feel free to contact us	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge