



- Use it in combination with stepped locating pin **PJP** (→ P.xxxx).

- Material/Finish



| | PJB |
|-----------|-----------------------------------|
| Main body | Steel (hardness: 60 HRC or above) |

Unit : mm

| Part Number | d 1 | L 2 | | | | | D | R | H | T | Applicable positioning pin PJP → P.xxxx | Mass (g) |
|---------------|------------|------------|----|----|----|----|----|---|----|---|--|-----------|
| | | 8 | 10 | 12 | 16 | 20 | | | | | | |
| PJB-5 | 5 | 8 | 10 | 12 | 16 | | 10 | 1 | 14 | 3 | PJP-5-*** | 7 - 11 |
| PJB-6 | 6 | 8 | 10 | 12 | 16 | | 10 | 1 | 14 | 3 | PJP-6-*** | 6.2 - 9.5 |
| PJB-8 | 8 | | 10 | 12 | 16 | 20 | 12 | 2 | 16 | 4 | PJP-8-*** | 9.9 - 15 |
| PJB-10 | 10 | | 10 | 12 | 16 | 20 | 15 | 2 | 19 | 4 | PJP-10-*** | 14 - 22 |
| PJB-12 | 12 | | | | 16 | 20 | 18 | 2 | 22 | 4 | PJP-12-*** | 27 - 37 |

- Part number specification

PJB-6-16

Product Code **1 2**

Cleanroom Wash & Packaging → P.xxxx

Not Available

Vibration Resistant → P.xxxx

Not Available

Laser Marking → P.xxxx

Not Available