


# SNSS-TF Hex Socket Head Cap Screws - PTFE Coating




Seizing Prevention Chemical-proof SUS Stainless steel



- Tightening property (reference)  
Part Number : SNSS-M5 - 25-TF

➔ P.xxxx



- Excellent chemical resistance.
- The coating has excellent lubricating ability and is suitable for prevention of seizing.
- Conforms to JIS B 1176, ISO 4762, and DIN 912.

### ● Application

Seizing prevention. FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

### ● Material/Finish



	SNSS-TF
Main Body	SUSXM7 (S.S. Grade : A2) PTFE(Polytetrafluoroethylene) Coating
Strength Class	A2-70

Unit : mm

Part Number	M (Coarse)		L													D1	L1	B	Mass (g)	
	Nominal of Thread <span style="color:red">◀1</span>	Pitch	5	6	8	10	12	16	20	25	30	35	40							
SNSS-M3-TF	M3	0.5															5.5	3	2.5	0.67 - 1.4
SNSS-M4-TF	M4	0.7															7	4	3	1.5 - 3.2
SNSS-M5-TF	M5	0.8															8.5	5	4	2.5 - 4.8
SNSS-M6-TF	M6	1															10	6	5	4.7 - 8.3
SNSS-M8-TF	M8	1.25															13	8	6	12 - 19
SNSS-M10-TF	M10	1.5															16	10	8	23 - 33

### ● Part number specification

## SNSS - M6 - 25 - TF

Product Code	<span style="color:red">◀1</span>	<span style="color:red">◀2</span>	Product Code
--------------	-----------------------------------	-----------------------------------	--------------

<b>1</b> Individual Sales ➔ P.xxxx	<b>2</b> Cleanroom Wash & Packaging ➔ P.xxxx	<b>3</b> Screw Length Adjustment ➔ P.xxxx	<b>4</b> Vibration Resistant ➔ P.xxxx	<b>5</b> Modification process for captive use ➔ P.xxxx
1 piece in 1 pack	Available / Add'l charge	Not Available	Not Available	Please feel free to contact us