



● Material/Finish



	<b>NSCSS-CP2</b>
Main Body	S45C Ferrosoferric Oxide Film (Black)
Hex Socket Head Cap Screw	SCM435 Ferrosoferric Oxide Film (Black)

- Set collars with mounting hole. Can be mounted to any machine or device, such as wheels, flanges and plates, by using the mounting hole.
- Split type. Because the shaft hole part can be fully split, mounting and removal are easy, with no damage to the shaft.
- Optimal for use with machines and devices that are difficult to disassemble.

Unit : mm

Part Number <sup>1</sup>	d	B	D	F	S*1	P	M (Coarse)*2	Mass (g)
<b>NSCSS-8-8-CP2</b>	8	8	25	8	4.5	16.5	M3	22
<b>NSCSS-8-10-CP2</b>	8	10	25	8	4.5	18	M4	28
<b>NSCSS-8-12-CP2</b>	8	12	28	8.5	5.5	18	M5	43
<b>NSCSS-8-15-CP2</b>	8	15	30	9	4.5	19	M6	61
<b>NSCSS-10-10-CP2</b>	10	10	30	9	5.5	20	M4	38
<b>NSCSS-10-12-CP2</b>	10	12	30	9	5.5	20	M5	47
<b>NSCSS-10-15-CP2</b>	10	15	35	10	5.5	22.5	M6	82
<b>NSCSS-12-10-CP2</b>	12	10	30	10	5.5	21	M4	37
<b>NSCSS-12-12-CP2</b>	12	12	30	10	5.5	21	M5	45
<b>NSCSS-12-15-CP2</b>	12	15	35	11	5.5	23.5	M6	80
<b>NSCSS-15-10-CP2</b>	15	10	32	11	5.5	24.5	M4	40
<b>NSCSS-15-12-CP2</b>	15	12	35	12	5.5	25	M5	61
<b>NSCSS-15-15-CP2</b>	15	15	40	13	5.5	27.5	M6	106
<b>NSCSS-16-10-CP2</b>	16	10	35	12	5.5	25.5	M4	48
<b>NSCSS-16-12-CP2</b>	16	12	35	12	5.5	25.5	M5	59
<b>NSCSS-16-15-CP2</b>	16	15	40	13	5.5	28	M6	104
<b>NSCSS-20-10-CP2</b>	20	10	40	14	5.5	30	M4	62
<b>NSCSS-20-12-CP2</b>	20	12	40	14	5.5	30	M5	75
<b>NSCSS-20-15-CP2</b>	20	15	45	15	5.5	32.5	M6	125
<b>NSCSS-25-12-CP2</b>	25	12	45	17	6.6	35	M5	87
<b>NSCSS-25-15-CP2</b>	25	15	50	18	6.6	37.5	M6	150
<b>NSCSS-30-15-CP2</b>	30	15	55	20	6.6	42.5	M6	167
<b>NSCSS-35-15-CP2</b>	35	15	60	23	6.6	47.5	M6	192
<b>NSCSS-40-18-CP2</b>	40	18	70	26	9	55	M8	316
<b>NSCSS-50-22-CP2</b>	50	22	85	32	11	67.5	M10	547

\*1: Mounting screws are not supplied. The customer is asked to prepare them.

\*2: Hex socket head cap screw for tightening is provided.

● Part Number Specification

**NSCSS-8-8-CP2**



Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Laser Marking
Not Available	Not Available	Not Available	Available / Add'l charge