

● Material/Finish



	CUPB
Bracket Body	A6063 Anodized
Cover	A6063 Anodized
Plate	Polyacetal (Black)
Push Button	Polyacetal (Black)



- Bracket for simple positioning when using vertical axis round pipes/round shafts.
- Push the push button to unlock the lock, smoothly move the bracket vertically, and release the push button to fix it in position.
- It can be moved upward without pushing the push button, just by applying force.
- Load capacity of up to 5 kg.

● Specifications

Unit : mm


	CUPB-30	CUPB-40
Applicable Round Pipe/Round Shaft Diameter	$\phi 30 \pm 0.64$	$\phi 40 \pm 0.64$
Push Button Press Count Resistance*1	20,000 Times	

*1 : Values are for reference only. They are not guaranteed values.

Unit : mm

Part Number ◀1	D	L1	L	Max. Load Weight (kg)	Mass (g)
CUPB-30	30	22	61	5	394
CUPB-40	40	27	71	5	403

● Mounting



⚠ Precautions for Use

- Mount to a vertical axis.
- CUPB requires vertical mounting. If mounted upside-down, CUPB cannot remain fixed onto round pipes/round shafts.
- It will prevent rotating movements, but it will not be able to remain completely fixed.
- CUPB is a product that uses friction fastening. In cases where oil, etc. adhered to the round pipe/round shaft causes the friction coefficient to decrease or if impact loads or vibrations occur, the maximum load weight may decrease.
- The surface may be scratched depending on the material and surface finish of the round pipe/round shaft.
- If excessive loads are applied, then the round pipe/round shaft may be scratched or CUPB may be damaged.



- Take care to pay attention to the vertical orientation when mounting.

● Related Products

Tablet PC holders DTAC-PB using brackets for round pipes CUPB are available.



● Part number specification

CUPB-30

