



Shaft bore process required



- Products with/without grip mounting holes can be selected by the end symbol of the part number.
 - AH** ——— With grip mounting hole
 - AH-N** ——— Without grip mounting hole
- There is no grip supplied with this product. Order a grip separately. P.xxxx

• Material/Finish



	AH
Main Body	AC4C

Unit : mm

Part Number With Grip Mounting Holes	M (Coarse)		p	Part Number Without Grip Mounting Holes	D	H	A	E	s	d	L	Number of Spokes	Mass (g)
	Nominal of Thread	Pitch											
AH-80	M5	0.8	33	AH-80-N	80	26	10	15	16	28	25		95
AH-100	M5	0.8	42	AH-100-N	100	26	11	15	15	33	25		215
AH-125	M6	1	53.5	AH-125-N	125	32	14	15	18	33	30	2	225
AH-140	M6	1	62	AH-140-N	140	32	14	15	18	38	30	2	335
AH-160	M8	1.25	68	AH-160-N	160	36	15	16	21	39	35	2	415
AH-200	M10	1.5	87.5	AH-200-N	200	41	16	17	25	47	40	3	720
AH-250	M10	1.5	112	AH-250-N	250	42	19	20	23	52	40	3	1070
AH-300	M10	1.5	137	AH-300-N	300	47	19	22	28	57	45	3	1360

• Recommended applicable grip

Part Number	Recommended applicable grip			
	GNTR	GTR	GTM	HS
AH-80	GNTR-18 - M5	GTR-18 - M5	GTM-18 - M5	HS-5
AH-100	GNTR-18 - M5	GTR-18 - M5	GTM-18 - M5	HS-5
AH-125	GNTR-19 - M6	GTR-19 - M6	GTM-19 - M6	HS-6
AH-140	GNTR-19 - M6	GTR-19 - M6	GTM-19 - M6	HS-6
AH-160	GNTR-24 - M8	GTR-24 - M8	GTM-24 - M8	HS-8
AH-200	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10
AH-250	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10
AH-300	GNTR-28 - M10	GTR-28 - M10	GTM-28 - M10	HS-10

• Part number specification

AH - 80 - N
 Product Code

Cleanroom Wash & Packaging P.xxxx	Vibration Resistant P.xxxx	Laser Marking P.xxxx	Modification of Shaft Hole Diameter P.xxxx
Please feel free to contact us	Not Available	Available / Add'l charge	Available / Add'l charge