


# D Offset Handwheels



Shaft bore process required



- Products with/without grip mounting holes can be selected by the end symbol of the part number.
  - D** — With grip mounting hole
  - D-N** — Without grip mounting hole
- There is no grip supplied with this product. Order a grip separately. → P.xxxx

### Material/Finish



	D
Main body	FC200 Chrome Plating

Unit : mm

Part Number With Grip Mounting Holes	M (Coarse)		p	Part Number Without Grip Mounting Holes	D	H	A	s	d	L	Number of Spokes	Mass (g)
	Nominal of Thread	Pitch										
<b>D-80</b>	M5	0.8	27	<b>D-80-N</b>	80	36	14	22	24	24	3	430
<b>D-100</b>	M5	0.8	35.5	<b>D-100-N</b>	100	39	15	24	30	25	3	630
<b>D-125</b>	M6	1	46.5	<b>D-125-N</b>	125	40	16	24	33	28	3	755
<b>D-140</b>	M6	1	53.5	<b>D-140-N</b>	140	44	17	27	35	30	3	1360
<b>D-150</b>	M8	1.25	56	<b>D-150-N</b>	150	46	18	28	35	32	3	1410
<b>D-160</b>	M8	1.25	61	<b>D-160-N</b>	160	46	18	28	37	32	3	1200
<b>D-200</b>	M10	1.5	77	<b>D-200-N</b>	200	60	24	36	43	41	3	2250
<b>D-250</b>	M10	1.5	101.5	<b>D-250-N</b>	250	63	25	38	50	42	5	3710
<b>D-300</b>	M12	1.75	122	<b>D-300-N</b>	300	66	26	40	56	45	5	6150
<b>D-315</b>	M12	1.75	128.5	<b>D-315-N</b>	315	72	28	44	60	49	5	6650

### Recommended applicable grip

Part Number	Recommended Applicable Grip*1	
	Plated Revolving Grip <b>RM</b>	Plated Fixing Grip <b>SM</b>
<b>D-80</b>		SM-5
<b>D-100</b>		SM-5
<b>D-125</b>	RM-6	SM-6
<b>D-140</b>	RM-6	SM-6
<b>D-150</b>	RM-8	SM-8
<b>D-160</b>	RM-8	SM-8
<b>D-200</b>	RM-10	SM-10
<b>D-250</b>	RM-10	SM-10
<b>D-300</b>	RM-12	SM-12
<b>D-315</b>	RM-12	SM-12

\*1: If a revolving grip other than the recommended applicable grip is used, the grip may not rotate.

### Part number specification

**D - 80 - N**  
 Product Code

Cleanroom Wash & Packaging → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx	Modification of Shaft Hole Diameter → P.xxxx
Not Available	Not Available	Not Available	Available / Add'l charge