



● Material/Finish



	NSCSS-SN2
Main Body	SUS304
Hex Socket Head Cap Screw	SUSXM7

● Part Number Specification

NSCSS-8-8-SN2



- Set collars with mounting hole (female screw). Can be mounted to any machine or device, such as wheels, flanges and plates, by using the mounting hole (female screw).
- Split type. Because the shaft hole part can be fully split, mounting and removal are easy, with no damage to the shaft.
- Optimal for use with machines and devices that are difficult to disassemble.

Unit : mm

Part Number	d	B	D	F	P	M (Coarse)*1	M1 (Coarse)*2		Mass (g)
							Nominal of Thread	Pitch	
NSCSS-8-8-SN2	8	8	25	8	16.5	M3	M3	0.5	24
NSCSS-8-10-SN2	8	10	25	8	18	M4	M4	0.7	29
NSCSS-8-12-SN2	8	12	28	8.5	18	M5	M4	0.7	46
NSCSS-8-15-SN2	8	15	30	9	19	M6	M4	0.7	63
NSCSS-10-10-SN2	10	10	30	9	20	M4	M4	0.7	41
NSCSS-10-12-SN2	10	12	30	9	20	M5	M4	0.7	50
NSCSS-10-15-SN2	10	15	35	10	22.5	M6	M4	0.7	86
NSCSS-12-10-SN2	12	10	30	10	21	M4	M4	0.7	39
NSCSS-12-12-SN2	12	12	30	10	21	M5	M4	0.7	49
NSCSS-12-15-SN2	12	15	35	11	23.5	M6	M4	0.7	84
NSCSS-15-10-SN2	15	10	32	11	24.5	M4	M4	0.7	42
NSCSS-15-12-SN2	15	12	35	12	25	M5	M4	0.7	65
NSCSS-15-15-SN2	15	15	40	13	27.5	M6	M4	0.7	111
NSCSS-16-10-SN2	16	10	35	12	25.5	M4	M4	0.7	51
NSCSS-16-12-SN2	16	12	35	12	25.5	M5	M4	0.7	63
NSCSS-16-15-SN2	16	15	40	13	28	M6	M4	0.7	108
NSCSS-20-10-SN2	20	10	40	14	30	M4	M5	0.8	64
NSCSS-20-12-SN2	20	12	40	14	30	M5	M5	0.8	76
NSCSS-20-15-SN2	20	15	45	15	32.5	M6	M5	0.8	129
NSCSS-25-12-SN2	25	12	45	17	35	M5	M5	0.8	91
NSCSS-25-15-SN2	25	15	50	18	37.5	M6	M5	0.8	156
NSCSS-30-15-SN2	30	15	55	20	42.5	M6	M6	1.0	171
NSCSS-35-15-SN2	35	15	60	23	47.5	M6	M6	1.0	195
NSCSS-40-18-SN2	40	18	70	26	55	M8	M8	1.25	324
NSCSS-50-22-SN2	50	22	85	32	67.5	M10	M8	1.25	571

*1 : Hex socket head cap screw for tightening is provided.

*2 : Mounting screws are not supplied. The customer is asked to prepare them.

Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Laser Marking
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge