


# SNFS-SUC Phillips Flat Head Screws for Sheet Metal



Protrusion **SUS** Stainless steel



● Material/Finish




|           |                               |
|-----------|-------------------------------|
|           | <b>SNFS-SUC</b>               |
| Main Body | SUSXM7 (Equivalent to SUS304) |




- Stainless steel Phillips flat head screws with cut seating surface.
- Suitable for sheet metal, preventing seating surface and incomplete threads from hitting the bottom when fixing sheet metal.

**Normal flat head machine screw**

**SNFS-SUC**



Incomplete thread part hits bottom



Cut seating surface prevents bottom hitting

- Incomplete thread part has no more than two peaks.
- Bolts for sheet metal are also available with special specifications such as dimensions, material, head shape, and so on. Please contact our customer service.
- Application

Reducing the size of equipment and devices


Unit : mm

| Part Number <span style="color:red">◀1</span> | M (Coarse)        |       | L <span style="color:red">◀2</span> |   |   |   |    |    |    | D1 | L1  | Cross-recessed Socket No. | Mass (g)    | Qty per Pack |
|-----------------------------------------------|-------------------|-------|-------------------------------------|---|---|---|----|----|----|----|-----|---------------------------|-------------|--------------|
|                                               | Nominal of Thread | Pitch | 4                                   | 5 | 6 | 8 | 10 | 12 | 15 |    |     |                           |             |              |
| <b>SNFS-M3-SUC</b>                            | M3                | 0.5   | 4                                   | 5 | 6 | 8 | 10 |    |    | 6  | 1.2 | 1                         | 0.32 - 0.42 | 50           |
| <b>SNFS-M4-SUC</b>                            | M4                | 0.7   | 4                                   | 5 | 6 | 8 | 10 | 12 |    | 8  | 1.5 | 2                         | 0.4 - 1.2   | 50           |
| <b>SNFS-M5-SUC</b>                            | M5                | 0.8   |                                     | 5 | 6 | 8 | 10 | 12 | 15 | 10 | 2   | 2                         | 1.7 - 3.2   | 20           |
| <b>SNFS-M6-SUC</b>                            | M6                | 1     |                                     |   | 6 | 8 | 10 | 12 | 15 | 12 | 2.3 | 2                         | 2.8 - 4.4   | 20           |

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

**SNFS-M5-12-SUC**



|                                                       |                                                                 |                                                   |                                                          |                                                                |
|-------------------------------------------------------|-----------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------------|
| <b>1</b> Individual Sales<br>Available / Add'l charge | <b>2</b> Cleanroom Wash & Packaging<br>Available / Add'l charge | <b>3</b> Screw Length Adjustment<br>Not Available | <b>4</b> Vibration Resistant<br>Available / Add'l charge | <b>5</b> Modification process for captive use<br>Not Available |
|-------------------------------------------------------|-----------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------------|