


SPA-LC Plastic screw - Hex Socket Low Head Bolt - RENY



Protrusion
 High strength
 High Specific Strength



● Material/Finish



	SPA-LC
Main body	RENY™*1 (Glass Fiber 50% Reinforced Polyamide MXD6) (Black)
Heat resistance temperature*2	105°C

*1: RENY™ is a trademark or registered trademark of Mitsubishi Gas Chemical Company, Inc.
 *2: A value of plastic materials. The allowable operating temperature of the product varies depending on use conditions such as tightening torque.

- Hex socket head cap screw with low head.
- For space-saving of equipment/device and applications with a limited top space.
- RENY™ is thermoplastic engineering plastics with excellent tensile strength and bending strength.
- It is highly fatigue-resistant and has excellent creeping and heat insulation properties.
- While it is nearly as strong as metal, its weight is approximately 1/5 of iron.
- The properties and precautions of plastic screws

● Application

Heat insulation and dew condensation prevention of electric and electronic devices / refrigerating and freezing facilities / Weight saving of offshore instruments, plating facility and automobile, aircraft and space equipment, etc.

Unit : mm

Part Number	M (Coarse)		L								D1	L1	B	Tension*1 Rupture Load (N)	Torsional*1 Torque (N·m)	Mass (g)	Qty per pack	
	Nominal of Thread 1	Pitch																
SPA-M3-LC	M3	0.5	6	8	10	12	16	20				5.5	2	2	799	0.2	0.11 - 0.25	20
SPA-M4-LC	M4	0.7	6	8	10	12	16	20	25			7	2.8	2.5	1286	0.74	0.24 - 0.58	20
SPA-M5-LC	M5	0.8	6	8	10	12	16	20	25	30		8.5	3.5	3	1976	1.08	0.39 - 1	20
SPA-M6-LC	M6	1			10	12	16	20	25	30	40	10	4	4	2767	2.26	0.75 - 2.1	20

*1: Values in chart are for reference only. They are not guaranteed values. The recommendation torque is 50% of the torsional torque.
 ● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

SPA - M5 - 30 - LC

Product Code	1	2	Product Code
--------------	------------------------------------	------------------------------------	--------------

Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available