




SRTRS Triangular Socket Button Head Cap Screws

Tamper Resistance **SUS** Stainless steel

● Material/Finish



	SRTRS
本体	SUS304相当
強度区分	A2-50相当



- Button head cap screws with triangular socket.
- This prevents mounting and removing with regular tools.
- Install and remove with **SRTRB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

● Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Unit : mm


Part Number 1	M (Coarse)		L 2							D1	L1	t	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	6	8	10	12	16	20	25							
SRTRS-M3	M3	0.5	6	8	10	12	16	20	25	5.7	1.65	0.95	SRTRB-3	SRD-6.35	0.43 - 1.1	10
SRTRS-M4	M4	0.7	6	8	10	12	16	20	25	7.6	2.2	1.3	SRTRB-4	SRD-6.35	0.89 - 2	10
SRTRS-M5	M5	0.8			10	12	16	20	25	9.5	2.75	1.5	SRTRB-5	SRD-6.35	2.1 - 4.1	10
SRTRS-M6	M6	1		8	10	12	16	20	25	10.5	3.3	1.8	SRTRB-6	SRD-6.35	2.5 - 5.9	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● **SRTRB** Dedicated bits


Unit : mm

Part Number	L	B	Mass (g)
SRTRB-3	32	6.35	5.8
SRTRB-4	32	6.35	6.4
SRTRB-5	32	6.35	6.5
SRTRB-6	32	6.35	7

SRTRB● **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD

● Part number specification

SRTRS-M5-16

1 Individual Sales → P.0000 Cleanroom Wash & Packaging → P.0000 Screw Length Adjustment → P.0000 Vibration Resistant → P.0000 Modification process for captive use → P.0000

Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge