




SNSI3T-UT Titanium Hex Socket Head Cap Screws with Captive Washers

Chemical-proof
 Non-Magnetic
 Lightweight
 Easy operation



● Material/Finish



	SNSI3T-UT
Screw Body	TW340 (Grade 2 Titanium)
Plain Washer*1	TP340 (Grade 2 Titanium)
Spring Washer	TW340 (Grade 2 Titanium)

*1: The material of **SNSI3T-M3-UT** is TP270 (grade 1 titanium).

● Mechanical Properties

	TW270 (Grade 1 Titanium)	TW340 (Grade 2 Titanium)
Tensile Strength (N/mm ²)	270 - 410	340 - 510
0.2% Proof Load (N/mm ²)	165 or More	215 or More
Elongation (%)	27 or More	23 or More

● Values in chart are for reference only. They are not guaranteed values.

● Physical Properties

	TW270 (Grade 1 Titanium) TW340 (Grade 2 Titanium)
Specific Gravity	4.51
Melting Point (°C)	1668
Longitudinal Elastic Modulus (GPa)	106
Thermal Conductivity (W/(m·K))	17.16
Linear Expansion Coefficient (K ⁻¹)	8.4×10^{-6}
Electric Resistance ($\mu\Omega \cdot m$)	0.55
Amplitude Permeability (μ)	1.0001 (Nonmagnetic)

● Values in chart are for reference only. They are not guaranteed values.



- Titanium hex socket head cap screws with captive washers.
- Plain washers and spring washers are integrated into the screws, preventing concerns about fallout issues. (Washer abbreviation: I=3)
- When using a washer in spot facing, workability is improved because the bolt and washer can be mounted and removed at the same time.
- The specific gravity is approximately 60% that of stainless steel.
- Non-magnetic.
- Excellent chemical resistance / seawater resistance.
- Application

Lighter-weight automobiles, aircrafts/aerospace equipment, robots, etc.
FPD production equipment / Semiconductor manufacturing equipment /
Electrical and electronic equipment / Offshore instruments / Plating facilities /
General industrial equipment


Unit : mm

Part Number	M (Coarse)		L							D ₁	D	L ₁	B	t	T (Approx.)	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	8	10	12	16	20	25	30								
SNSI3T-M3-UT	M3	0.5	8	10	12	16				5.5	7	3	2.5	0.5	0.7	0.58 - 0.79	10
SNSI3T-M4-UT	M4	0.7	8	10	12	16	20			7	9	4	3	0.8	1	1.3 - 1.8	10
SNSI3T-M5-UT	M5	0.8		10	12	16	20	25		8.5	10	5	4	1	1.3	2 - 3.2	10
SNSI3T-M6-UT	M6	1			12	16	20	25	30	10	12.5	6	5	1.5	1.5	4.1 - 5.9	10

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SNSI3T-M3-10-UT



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Not Available