




SPC-N




SPC-N

SPC-W



SPC-W



- Material/Finish



	SPC-N / SPC-W
Main body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

*1: This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Max. Operating Temperature*1 (min./max.): -40/115°C
- PC has low water absorbency and excellent weather resistance.
- The properties and precautions of plastic screws
→ P.xxxx
- Application

Electrical and electronic equipment and automobiles

SPC-N Hex Nuts

Unit : mm

Part Number ◀1	M (Coarse)		B	T	Mass (g)	Qty per pack
	Nominal of Thread	Pitch				
SPC-M2-N	M2	0.4	4	1.6	0.019	50
SPC-M2.6-N	M2.6	0.45	5	2	0.043	50
SPC-M3-N	M3	0.5	5.5	2.4	0.052	50
SPC-M4-N	M4	0.7	7	3.2	0.12	50
SPC-M5-N	M5	0.8	8	4	0.18	50
SPC-M6-N	M6	1	10	5	0.37	20
SPC-M8-N	M8	1.25	13	6.5	0.37	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

SPC-W Washers

Unit : mm

Part Number ◀1	d	D	t	Nominal	Mass (g)	Qty per pack
SPC-2-W	2.1	4	0.5	2	0.0055	100
SPC-2.6-W	2.7	6	0.5	2.6	0.01	100
SPC-3-W	3.3	8	0.8	3	0.04	100
SPC-4-W	4.5	10	0.8	4	0.06	100
SPC-5-W	5.5	12	0.8	5	0.086	100
SPC-6-W	6.5	13	1	6	0.12	50
SPC-8-W	8.5	18	1.6	8	0.33	50

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

- Part number specification

SPC-M4-N

◀1

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available