

● Material/Finish



SPM-B	
Main Body	S45C Full Quenching (Hardness: 35 HRC or Above) Trivalent Chromate Treatment


- For workpiece stopper applications.
- The bolt features a rounded hexagonal head.
- Fully quenched. It has excellent wear resistance.

Unit : mm

Part Number	M (Coarse)		L3	L1	L	B	C (Approx.)	R	Mass (g)
	Nominal of Thread	Pitch							
SPM-M3-B	M3	0.5	7	2	5	6	6.9	7.5	0.6
SPM-M4-B	M4	0.7	8.8	2.8	6	7	8.1	8.5	1.2
SPM-M5-B	M5	0.8	10.5	3.5	7	8	9.2	10	2.2
SPM-M6-B	M6	1	12	4	8	10	11.5	12	3.7
SPM-M8-B	M8	1.25	15	5	10	13	15	16	8
SPM-M10-B	M10	1.5	20	6	14	17	19.6	22	16.8
SPM-M12-B	M12	1.75	23	7	16	19	21.9	25	26

● Usage Example

For workpiece stopper applications.



● Part Number Specification

SPM-M10-B



Cleanroom Wash & Packaging Not Available	Screw Combination Not Available	Screw Length Adjustment Not Available	Vibration Resistant Available / Add'l charge
---	------------------------------------	--	---