


SPMJ-B Rounded Head Stopper Bolts - Stainless Steel SUS420J2



SUS Stainless steel



Material/Finish




SPMJ-B

Main Body SUS420J2 Full Quenching (Hardness: 54 HRC or Above)


- For workpiece stopper applications.
- The bolt features a rounded hexagonal head.
- SUS420J2 (fully quenched). It has excellent wear resistance.

Unit : mm

Part Number 	M (Coarse)		L3	L1	L	B	C (Approx.)	R	Mass (g)
	Nominal of Thread	Pitch							
SPMJ-M5-B	M5	0.8	10.5	3.5	7	8	9.2	10	2.1
SPMJ-M6-B	M6	1	12	4	8	10	11.5	12	3.6
SPMJ-M8-B	M8	1.25	15	5	10	13	15	16	7.8
SPMJ-M10-B	M10	1.5	20	6	14	17	19.6	22	16.6
SPMJ-M12-B	M12	1.75	23	7	16	19	21.9	25	25.7

Usage Example

For workpiece stopper applications.



Part Number Specification

SPMJ-M10-B



Cleanroom Wash & Packaging Please feel free to contact us	Screw Combination Not Available	Screw Length Adjustment Not Available	Vibration Resistant Available / Add'l charge
--	------------------------------------	--	---