

● Material/Finish



	SPMJ
Main Body	SUS420J2 Full Quenching (Hardness: 54 HRC or Above)/ End Face Polishing


- Use as a recipient of the stopper bolt **SSBS-B** and stopper screw **SANS-B**.
- SUS420J2 (fully quenched). It has excellent wear resistance.

Unit : mm

Part Number	M (Coarse)		L ₃	L ₁	L	B	C (Approx.)	Mass (g)
	Nominal of Thread	Pitch						
SPMJ-M5	M5	0.8	10.5	3.5	7	8	9.2	2.3
SPMJ-M6	M6	1	12	4	8	10	11.5	4
SPMJ-M8	M8	1.25	15	5	10	13	15	8.7
SPMJ-M10	M10	1.5	20	6	14	17	19.6	18.3
SPMJ-M12	M12	1.75	23	7	16	19	21.9	28.1

● Usage Example

In combination with stopper screw **SANS-B**.



● Part Number Specification

SPMJ-M10



Cleanroom Wash & Packaging Please feel free to contact us	Screw Combination Not Available	Screw Length Adjustment Not Available	Vibration Resistant Available / Add'l charge
--	------------------------------------	--	---