




SROS One Side Pan Head Machine Screws

Tamper Resistance **SUS** Stainless steel



- The screws can be installed, but not removed, using commercially available slotted screwdrivers.
- Remove the screws by using **SROT** Specialty Removal Tool.

• Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

• Material/Finish



SROS	
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Unit : mm


Part Number ◀1	M (Coarse)		L ◀2										D1	L1	Dedicated Removal Tool	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch															
SROS-M3	M3	0.5	5	6	8	10	12	16					5.5	2	SROT-410	0.49 - 0.94	20
SROS-M4	M4	0.7		6	8	10	12	16	20	25	7	2.6	SROT-410	1 - 2.5	20		
SROS-M5	M5	0.8			8	10	12				9	3.3	SROT-510	2.2 - 2.7	20		

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• SROT Dedicated Screwdriver

Unit : mm

Part Number	b	Mass(g)
SROT-410	8	94
SROT-510	9.5	127



• Grip color may vary depending on the lot.

• Part number specification

SROS-M4-16



1 Individual Sales → P. xxxxx	2 Cleanroom Wash & Packaging → P. xxxxx	3 Screw Length Adjustment → P. xxxxx	4 Vibration Resistant → P. xxxxx	5 Modification process for captive use → P. xxxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge